

# GEN-IUI WS™

## Portable IUI Workstation

HEPA Filter  
99.97%



Antistatic -  
polycarbonate



Sanitary  
stainless steel

- Economical and easy to IUI Workstation
- Air cleaning systems are maintained using the EFU
- Polycarbonate material used is not broken (external)
- Sanitary stainless steel bottom
- Ease the exchange of HEPA Filter(99.97%)



**IVF Gen**


*Contribution 2 next Generation*

IVF GEN Australia- Phone : +61 413 665 905

Email : [info@ivfgen.com](mailto:info@ivfgen.com), [ivfgen@gmail.com](mailto:ivfgen@gmail.com), Website : [www.ivfgen.com](http://www.ivfgen.com)

# GEN-IUI WS™

## Portable IUI Workstation



\* May differ from the actual product.

- Air cleaning systems are maintained using the EFU
- Polycarbonate material used is not broken (external)
- Sanitary stainless steel bottom
- Ease the exchange of HEPA Filter(99.97%)

## Specifications

Product	GEN-IUI WS 700™	GEN-IUI WS 1200™
Dimensions(WxDxH)	750 x 500 x 750mm	1200 x 750 x 750mm
Wind Speed	0.3 m/s	
External	Polycarbonate	
Working Area	Stainless steel	
Lamp	LED	
HEPA Filter	Remove 99.97% of all airborne particles down to 0.3µm	
Power	220V	
Weight	15Kg	25Kg



**IVF Gen**

*Contribution 2 next Generation*

**IVF GEN Australia- Phone : +61 413 665 905**  
**Email : info@ivfgen.com, ivfgen@gmail.com**  
**Website : www.ivfgen.com**